



*We invent,  
you succeed !*



## MECASONIC Instrumentation

### For motor attachment :

- The MECASONIC® fits to any motor type (air or electric) corresponding to ISO standards. Frequency of vibration increases gradually with motor speed.  
**Ideal motor speed: 30 000 rpm. -**
- Press button-head. Excellent visibility due to reduced head size. Remarkable access due to the small head and neck assembly.
- To fit the sonic instrument, press the button and release it, once the instrument is secure.
- Working length adjustment at 0.5 mm, either manually thanks to scores on the shaft or with the MICRO-MEGA gauge.
- Water from Dental unit can be used for irrigation.



### MECASONIC MM 1400

#### Supplied with :

1 plate MECA-SHAPER® and 1 plate MECA-RISPI®.





**MECA-RISPI®**



Length 17 - 21 - 25 - 29 mm  
Individual Sizes : n° 0 to 6  
Assortment : from 1 to 6



**MECA-SHAPER®**



Length 17 - 21 - 25 - 29 mm  
Individual Sizes : n° 10 to 40  
Assortment : from 15 to 40

